

FIELD ENGINEERING SUPPORT SOUTHBORO

## Technical Information Bulletin

DATE:

28 OCTOBER 1973

FROM:

R. C. JENSEN

SUBJECT:

NOVA 1200 POWER MONITOR AUTO

RESTART OPTION (8106)

NUMBER: S1005

CATEGORY:PROCESSER OPTIONS

MODEL:

8106

It has come to the attention of this writer, by the LA Office, that an improper component may have been installed in this option. Ensure that Cl (Cap in lower left corner of board next to Ul) is 6.8 ufd cap and not a 1.0 ufd cap. The components are physically the same size.

2011 6354-48

74013